

# MSR Gold™ FastFit

## MSR Gold™ 1500/1 FastFit



All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

## Product data

### • General Characteristics

System Description	FastFit
Cap-Base	PGJX50
Cap-Base Information	PGJX50
Execution	-
Operating Position	any
Main Application	Entertainment
Life to 50% failures	750 hr
EM	
Non-household	For professional use only-not for domestic use
Symbol	

### • Light Technical Characteristics

Color Code	1
Color Rendering Index	85 Ra8
Color Temperature	5700 K
Chromaticity Coordinate X	328 -
Chromaticity Coordinate Y	334 -
Luminous Flux Lamp EM	114750 (min), 127500 (nom) Lm
Luminous Efficacy Lamp EM	85 Lm/W

### • Electrical Characteristics

Lamp Wattage	1500 W
Lamp Wattage Technical	1500.0 W
Lamp Current	15.3 A
Ignition Supply Voltage	198 (min) V

Dimmable Yes

### • Luminaire Design Requirements

Pinch Temperature	500 (max) C
Bulb Temperature	950 (max) C

### • Product Dimensions

Overall Length C	128 (max) mm
Diameter D	28 (max) mm
Width F	50 mm
Light Center Length L	64 (min), 65 (nom), 66 (max) mm
Arc Length O	6.3 mm

### • Product Data

Order code	928108905115
Full product code	928108905115
Full product name	MSR Gold™ 1500/1 FastFit
Order product name	MSR Gold 1500/1 FastFit 1CT/4
Pieces per pack	1
Packing configuration	4
Packs per outerbox	4
Bar code on pack - EAN1	8718696402757
Bar code on outerbox - EAN3	8718696402764
Logistic code(s) - 12NC	928108905115
Net weight per piece	0.133 kg


# PHILIPS

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and


remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing




MSR Gold™ 1500/1 FastFit

Product	A (Min)	A (Norm)	A (Max)	C (Max)	D (Max)	D1 (Norm)	F (Min)	F (Norm)	F (Max)	L (Min)	L (Norm)	L (Max)	O (Norm)
MSR GOLD 1500/1 FastFit	-	-	-	128	28	-	-	50	-	64	65	66	6.3




PGJX50

Photometric data



MSR Gold™ 1500 FastFit



MSR Gold™ 1500 FastFit



© 2015 Koninklijke Philips N.V. (Royal Philips)  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2015, September 27  
data subject to change